



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	10
Wire Size/AWG	34 - 28
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.50 mm
Size	1P
Suggested matching part	<a href="#">PLG.M1.0SL.LG</a>
Series	REDEL P - Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m1-0sl-ac65g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m1-0sl-ac65g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Solder
R (max)	8.5 mOhm
Insert configuration value	1P.M10 - 10 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	3 A
Test voltage contact-contact	1.2 (kV DC)
Max. Solid Conductor	0.09 mm <sup>2</sup> (AWG 28)
Max. Stranded Conductor	0.09 mm <sup>2</sup> (AWG 28)
Air clearance	0.55 mm
Creepage distance	0.55 mm
Bucket Dia.	0.45 mm (0.018in)
Contact Dia.	0.5 mm (0.0201in)
Wire Size/AWG	34 - 28
Gender	Standard

## Form & Material

Shell style / Model id	PA - Straight plug with cable collet
Plug	Straight
Housing material	PEI (Polyetherimide), grey
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Grey collet nut
Weight	4.91 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m1-0sl-ac65g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m1-0sl-ac65g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +170°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.50 mm

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.10.T28.053QGZE	TPR (medical)	Grey	
110280	PVC	Black	

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m1-0sl-ac65g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m1-0sl-ac65g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.