



## Summary

[Request a quote](#)

[Catalog](#)

Thermocouple	2
Wire Size/AWG	30 - 22
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.30 - 4.10 mm
Size	0S
Matching parts	<a href="#">FFA.0S.302.CLKL42</a>
Series	S - Indoor Stepped Insert

## Technical details

### Electrical Configuration

Thermocouple	2
Insert configuration value	0S.302/ThC - 1 Thermocouple Pair
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	10 Amps
ThC. Materials (P+/N-)	Chromel / Alumel
Contact Dia.	0.9
Wire Size/AWG	30 - 22

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/pca-0s-302-clkl42.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pca-0s-302-clkl42.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Form & Material

Shell style / Model id	PCA - Free receptacle, cable collet
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	8.53 g


## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	3.30 - 4.10 mm

## Drawings



[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/pca-0s-302-clk42.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pca-0s-302-clk42.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>A</b>	<b>L</b>	<b>S2</b>	<b>C</b>
mm.	8.9	33.5	6.5	4.2
in.	0.35	1.32	0.26	0.17

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/pca-0s-302-clk142.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pca-0s-302-clk142.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.