



Image for illustrative purpose only

Summary

[Request a quote](#)

[REDEL T7 en](#)

Nb of contacts Triax	1
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Size	T7
Suggested matching part	FAZ.T7.675.CTA04CZ

https://www.lemo.com/int_en/pcz-t7-675-ctl04cz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Rated current	12 A
Impedance	75 Ohms

Form & Material

Shell style / Model id	PCZ - Free socket, collet clamp, nut for fitting a bend relief
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	219.04 g

Environment

Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 20000 Hz]
Salt Spray Corrosion	>1000 hr


Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

Drawings

https://www.lemo.com/int_en/pcz-t7-675-ctl04cz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Dimensions

	A	L	S1	S2
mm.	23.5	87.5	22	20
in.	0.93	3.44	0.87	0.79

https://www.lemo.com/int_en/pcz-t7-675-ctf04cz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.