



Summary

[Request a quote](#)

[Catalog](#)

Fiber optic	2
Number of contacts Low Voltage	2
Number of contacts High Voltage	2
Wire Size/AWG	24 - 20
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	8.90 - 9.50 mm
Size	3K
Series	3K.93C.Y - SMPTE Hybrid

Technical details

https://www.lemo.com/int_en/solutions/specialties/3k-93c-y-smpte-hybrid/pew-3k-93c-ysec96z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Electrical Configuration

Contact Termination Low voltage	Crimp
Fiber optic	2
Insert configuration value	3K.93C - 2 FO Type F2, 2 HV + 2 LV
Rated current	10 Amps
Cable type	Cable type: A SMPTE 311M or EBU R100 S
Number of contacts Low Voltage	2
Number of contacts High Voltage	2
Wire Size/AWG	24 - 20

Form & Material

Shell style / Model id	PE - Fixed receptacle, nut fixing, cable adapter, with bend relief nut (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Special housing (see notes for details)
Locking system	Push-pull
Keying	5 keys (alpha=95, beta=115, gamma=20, delta=30, plug: female LV, male HV, female FO contacts)
Variant	Nut for fitting a bend relief
Weight	104.45 g

Environment

Environmental protection (IP rating)	IP68
Minimal temperature	-40°C / +80°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]



Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	8.90 - 9.50 mm

https://www.lemo.com/int_en/solutions/specialties/3k-93c-y-smpte-hybrid/pew-3k-93c-ysec96z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	M	E	A	L
mm.	4.5	7.5	30	135
in.	0.18	0.3	1.18	5.31

https://www.lemo.com/int_en/solutions/specialties/3k-93c-y-smpte-hybrid/pew-3k-93c-ysec96z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.