



## Summary

[Request a quote](#)

[Catalog](#)

Thermocouple	6
Wire Size/AWG	22 - 14
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	12.90 - 13.50 mm
Size	4K
Series	K - Outdoor keyed

## Technical details

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/phc-4k-306-cykc13.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/phc-4k-306-cykc13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Thermocouple	6
Contact Termination Thermocouple	Crimp
Insert configuration value	4K.306 - 3 Thermocouple Pairs
Insulator	Y: PEEK for crimp contacts
Rated current	24 Amps
Contact Dia.	2 mm (0.079" in)
Wire Size/AWG	22 - 14
Gender	Standard

## Form & Material

Shell style / Model id	PH - Free receptacle, cable collet
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	2 keys (alpha=60, plug: male contacts, receptacle: female contacts)
Weight	153.67 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/phc-4k-306-cykc13.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/phc-4k-306-cykc13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	12.90 - 13.50 mm

## Drawings



## Dimensions

	<b>S2</b>	<b>L</b>	<b>A</b>
mm.	19	75.5	29
in.	0.75	2.97	1.14

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/phc-4k-306-cykc13.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/phc-4k-306-cykc13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.