

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|-----------------------------------|
| Thermocouple | 16 |
| Wire Size/AWG | 30 - 22 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Free |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 9.30 - 9.90 mm |
| Size | 2B |
| Matching parts | FGG.2B.316.CYKD99 |
| Series | B - Indoor keyed |

Technical details

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/phg-2b-316-cykd99.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Electrical Configuration

| | |
|----------------------------|----------------------------|
| Thermocouple | 16 |
| Insert configuration value | 2B.316 - 16 Low Voltage |
| Insulator | Y: PEEK for crimp contacts |
| Rated current | 6 Amps |
| ThC. Materials (P+/N-) | Chromel / Alumel |
| Contact Dia. | 0.7 |
| Wire Size/AWG | 30 - 22 |
| Gender | Standard |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | PH - Free receptacle, cable collet |
| Socket / Receptacle | Free |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Weight | 40.32 g |

Environment

| | |
|--------------------------------------|--|
| Technical domain | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental protection (IP rating) | IP50 |
| Minimal temperature | -55°C / +250°C |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 75 dB (10 MHz) |
| Shielding (min) | 40 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |
| Salt Spray Corrosion | >1000 hr |


https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/phg-2b-316-cykd99.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

| | |
|------------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 9.30 - 9.90 mm |

Drawings



Dimensions

| | S2 | S1 | L | A |
|-----|-----------|-----------|----------|----------|
| mm. | 12 | 13 | 47 | 16.5 |
| in. | 0.47 | 0.51 | 1.85 | 0.65 |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/phg-2b-316-cykd99.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.