



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	2
Wire Size/AWG	16 - 12
Gender	Reverse Gender
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.20 mm
Size	2B
Suggested matching part	<a href="#">FHJ.2B.302.CYMD62Z</a>
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	2
Contact Termination Low voltage	Crimp
R (max)	3.3 mOhm
Insert configuration value	2B.302 - 2 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	20.5 A
Vtest (contact-contact)	4.1 kV (DC)
Vtest (contact-shell)	3.8 kV (DC)
Contact retention	65 N
Max. Conductor	2.5 mm <sup>2</sup> (AWG 12)
Min. Conductor	1.5 mm <sup>2</sup> (AWG 16)
Bucket Dia.	2.4 mm (0.094in)
Contact Dia.	2 mm (0.079in)
Wire Size/AWG	16 - 12
Gender	Reverse Gender

## Form & Material

Shell style / Model id	PH - Free receptacle, cable collet and nut for fitting a bend relief
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	2 keys (alpha=37.5, plug: female contacts, receptacle: male contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	39.19 g

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.20 mm

# Recommended By Lemo

## Accessories

Replacement contact	<a href="#">FGG.2B.575.ZZC</a>
Compatible cap	<a href="#">BRF.2S.200.NAS</a>





## Tools

Positionner	<a href="#">DCE.91.202.BVCM</a>
Extraction tool	<a href="#">DCC.20.25B.LAG</a>
Crimp tool	<a href="#">DPC.91.101.A</a>
Spanner wrench	<a href="#">DCD.2B.ZZZ.PA120</a>

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
102080	PVC	Grey	
120184	PVC	Black	
120500	PVC	Grey	
120751	PVC	Grey	
220750	PVC	Grey	

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/phj-2b-302-cycd62z.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.