



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	14
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	1P
Suggested matching part	<a href="#">PAC.M1.4GL.AC52G</a>
Series	REDEL P - Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pkc-m1-4gl-vz.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkc-m1-4gl-vz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	14
Contact Termination Low voltage	PCB - Elbow
R (max)	8.5 mOhm
Insert configuration value	1P.M14 - 14 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2 A
Test voltage contact-contact	0.85 (kV DC)
Air clearance	0.5 mm
Creepage distance	0.5 mm
Contact Dia.	0.5 mm (0.0201in)
Gender	Standard

## Form & Material

Shell style / Model id	PK - Fixed receptacle with two nuts (back panel mounting), 90° print contacts
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	PSU (Polysulfone), grey
Locking system	Push-pull
Keying	C: 2 keys (alpha=80, Plug: male contacts, Receptacle: female contacts)
Variant	without front nut
Weight	6.69 g




## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +150°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us.

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pkc-m1-4gl-vz.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkc-m1-4gl-vz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Dimensions

	A	L	N
mm.	19.5	5.2-12.9	20.5
in.	0.77		0.81

# Recommended By Lemo

### Accessories

Compatible cap	<a href="#">PBG.200.BMV</a>
----------------	-----------------------------

### Tools

Spanner	<a href="#">POB.186.GN</a>
---------	----------------------------

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pkc-m1-4gl-vz.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkc-m1-4gl-vz.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.