



Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|---|
| Number of contacts Low Voltage | 4 |
| Wire Size/AWG | 24 - 20 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 6.10 - 6.50 mm |
| Size | 1K |
| Suggested matching part | FGG.1K.304.CYCC65Z |
| Series | K - Outdoor keyed |

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/pkg-1k-304-cymc65z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------------|
| Contact Termination Low voltage | Crimp |
| R (max) | 4.8 mOhm |
| Insert configuration value | 1K.304 - 4 Low Voltage |
| Insulator | Y: PEEK for crimp contacts |
| Rated current | 10 A |
| Vtest (contact-contact) | 1700 V (AC), 2400 V (DC) |
| Vtest (contact-shell) | 1800 V (AC), 2550 V (DC) |
| Contact retention | 30 N |
| Contact Type | Crimp |
| Max. Conductor | 0.5 mm ² (AWG 20) |
| Min. Conductor | 0.25 mm ² (AWG 24) |
| Bucket Dia. | 1.1 mm (0.043in) |
| Contact Dia. | 0.9 mm (0.035in) |
| Number of contacts Low Voltage | 4 |
| Wire Size/AWG | 24 - 20 |
| Gender | Standard |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | PK - Fixed receptacle, nut fixing, cable collet and nut for fitting a bend relief |
| Socket / Receptacle | Fixed Panel Front Mounted |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces |
| Locking system | Push-pull |
| Keying | 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Weight | 34.62 g |

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/pkg-1k-304-cymc65z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

| | |
|-----------------------------------|---|
| Technical domain | Audio Video, Energy and Industrial, Medical, Test and Measurement |
| Environmental sealing (IP rating) | IP68 |
| Endurance | 5000 mating cycles |
| Temperature range | -55°C / +200°C |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 95 dB (10 MHz) |
| Shielding (min) | 80 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |
| Salt Spray Corrosion | >1000 hr |

Cable fixation

| | |
|------------------------------------|-----------------------|
| Cable termination protection | For cable bend relief |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 6.10 - 6.50 mm |

Drawings



Dimensions

| | A | B | e | E | L | M | S1 | S2 | S3 |
|-----|------|------|---------|------|------|------|------|------|------|
| mm. | 20 | 21.5 | M16x1.0 | 9.5 | 46.2 | 4.5 | 14.5 | 9 | 19 |
| in. | 0.79 | 0.85 | | 0.37 | 1.82 | 0.18 | 0.57 | 0.35 | 0.75 |

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/pkg-1k-304-cymc65z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories

| | |
|---------------------|--------------------------------|
| Replacement contact | EGG.1B.660.ZZM |
|---------------------|--------------------------------|

Tools

| | |
|-------------|--------------------------------|
| Positionner | DCE.91.091.BVM |
|-------------|--------------------------------|

| | |
|-----------------|--------------------------------|
| Extraction tool | DCC.09.05B.LAG |
|-----------------|--------------------------------|

| | |
|------------|------------------------------|
| Crimp tool | DPC.91.701.V |
|------------|------------------------------|

| | |
|----------------|----------------------------------|
| Spanner wrench | DCD.1E.ZZZ.PA090 |
|----------------|----------------------------------|

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|----------|--------|---|
| 240500 | PVC | Grey |  |
| 417920 | PVC | Grey |  |
| CTR.75.030.121870G | PVC | Grey |  |

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/pkg-1k-304-cymc65z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.