



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|---------------------|-----------|
| Nb of contacts Coax | 1 |
| Locking system | Push-pull |
| Size | 0A |

https://www.lemo.com/int_en/pls-0a-275-ntlz41.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|----------------------------|--------------------------|
| Nb of contacts Coax | 1 |
| Contact Termination Coax | Solder |
| Insert configuration value | 0A.275 - 1 Coax (75 Ohm) |
| Rated current | 2 A |
| OHM | 75 |
| Bucket Dia. | 0.65 |

Form & Material

| | |
|------------------|---|
| Housing material | Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | 3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts) |
| Colour | Grey |
| Weight | 7.59 g |

Environment

| | |
|-----------------------------------|--------------------|
| Environmental sealing (IP rating) | IP50 |
| Endurance | 5000 mating cycles |
| Salt Spray Corrosion | >144 hr |

Cable fixation

| | |
|------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
|------------------------------|--|

https://www.lemo.com/int_en/pls-0a-275-ntlz41.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.