



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Wire Size/AWG	32 - 24
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.30 - 3.70 mm
Size	0S
Suggested matching part	<a href="#">FFA.0S.304.CLAC37</a>
Series	S - Indoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-clic37.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-clic37.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	Solder
R (max)	6.1 mOhm
Insert configuration value	0S.304 - 4 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 A
Vtest	1060 V (AC), 1500 V (DC)
Contact Type	Solder
Max. Solid Conductor	0.25 mm <sup>2</sup> (AWG 24)
Max. Stranded Conductor	0.14 mm <sup>2</sup> (AWG 26)
Bucket Dia.	0.6 mm (0.024in)
Contact Dia.	0.7 mm (0.028in)
Number of contacts Low Voltage	4
Wire Size/AWG	32 - 24

## Form & Material

Shell style / Model id	PSA - Fixed receptacle, nut fixing, cable collet
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Colour	Grey
Weight	7.92 g

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-cllc37.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-cllc37.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	3.30 - 3.70 mm

## Drawings



## Dimensions

	A	B	e	E	L	M	S1	S2	S3	C
mm.	10	12.5	M9x0.6	7	33.5	1.2	8.2	6.5	11	4.2
in.	0.39	0.49		0.28	1.32	0.05	0.32	0.26	0.43	0.17

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-cllc37.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-cllc37.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---



### Tools

---

Spanner wrench

[DCD.0S.ZZZ.PA065](#)

## Cables

Cable PartNumber	Material	Colour	Cable image
40080	PVC	Black	
40086	PVC	Blue	
40240	PTFE	White	
4260	PTFE	White	

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-cllc37.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/psa-0s-304-cllc37.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.