



## Summary

[Request a quote](#)

---

[Catalog](#)

---

Nb of contacts Triax	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.10 - 7.50 mm
Size	1E
Series	E - Outdoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-650-ctlk75.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-650-ctlk75.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Insert configuration value	1E.650 - 1 Triax (50 Ohm)
Insulator	T: PTFE
Rated current	6 A
Impedance	50 Ohm
VSWR	1.01 + 0.17 * f/GHz
Vtest	1200 V (AC), 1690 V (DC)
Contact Type	Solder
Cable type	RGT 178, RGT 174,Belden 9222

## Form & Material

Shell style / Model id	PSA - Fixed receptacle, nut fixing, oversize cable collet
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	46.03 g

## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr


[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-650-ctlk75.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-650-ctlk75.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.10 - 7.50 mm

## Drawings



[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-650-ctlk75.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-650-ctlk75.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.