



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.20 - 4.20 mm
Size	1S
Suggested matching part	<a href="#">FFA.1S.120.CTAC42</a>
Series	S - Indoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/psa-1s-120-ctlc42.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/psa-1s-120-ctlc42.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	Solder
Insert configuration value	1S.120 - 1 Low Voltage
Insulator	T: PTFE
Rated current	18 A
Vtest (contact-contact)	1800 V (AC), 2550 V (DC)
Vtest (contact-shell)	1800 V (AC), 2550 V (DC)
Contact Type	Solder
Number of contacts Low Voltage	1

## Form & Material

Shell style / Model id	PSA - Fixed receptacle, nut fixing, cable collet
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	16.06 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr


[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/psa-1s-120-ctlc42.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/psa-1s-120-ctlc42.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	3.20 - 4.20 mm

## Drawings



## Dimensions

	A	B	e	E	L	M	S1	S2	S3	C
mm.	14	16	M12x1.0	7.5	40.5	1.5	10.5	8.5	14	6.2
in.	0.55	0.63		0.3	1.59	0.06	0.41	0.33	0.55	0.24

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/psa-1s-120-ctlc42.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/psa-1s-120-ctlc42.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.