



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|---|
| Number of contacts High Voltage | 1 |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 4.20 - 5.20 mm |
| Size | 1Y |
| Suggested matching part | FFA.1Y.405.CTAC52 |
| Series | Y - High Voltage Unipole |

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/psa-1y-405-ctlc52.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|----------------------------------|-------------------------|
| Number of contacts High Voltage | 1 |
| Contact Termination High voltage | Solder |
| Insert configuration value | 1Y.405 - 1 High Voltage |
| Insulator | T: PTFE |
| Rated current | 8 A |
| Test voltage (kV DC) | 10.5 |
| Creepage distance | 16 mm |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | PSA - Fixed receptacle with cable collet, nut fixing |
| Socket / Receptacle | Fixed Panel Front Mounted |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | Circular |
| Colour | Grey |
| Weight | 46.67 g |

Environment

| | |
|-----------------------------------|-----------------------|
| Technical domain | Specialties and Other |
| Environmental sealing (IP rating) | IP50 |
| Salt Spray Corrosion | >1000 hr |

Cable fixation

| | |
|------------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 4.20 - 5.20 mm |

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/psa-1y-405-ctlc52.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.