



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Triax	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Threaded
Jacket cable outside diameter [mm]	5.60 - 6.00 mm
Size	1V
Suggested matching part	FVN.1V.650.CLAC60

https://www.lemo.com/int_en/psn-1v-650-cllc60.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Insert configuration value	1V.650 - 1 Triax (50 Ohm)
OHM	50

Form & Material

Shell style / Model id	PSN - Fixed socket, cable collet, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	Circular, female
Colour	Grey
Weight	35.88 g

Environment

Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C
Climatical Category	20/200/21
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr


Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	5.60 - 6.00 mm

https://www.lemo.com/int_en/psn-1v-650-cllc60.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	A	B	e	E	L	M	N	S1	S3	S4
mm.	21	21.5	M16x1.0	10.5	46	2	8	14.5	9	19
in.	0.83	0.85		0.41	1.81	0.08	0.31	0.57	0.35	0.75

Recommended By Lemo

Accessories

Compatible cap	BRE.1V.200.NAV
----------------	--------------------------------