



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Size	2B
Suggested matching part	FFS.2B.250.ZTCE30
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/pss-2b-250-ztme30.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax	Crimp
Insulator	T: PTFE
Rated current	2 A
OHM	50
Max. Dielectric Dia.	1.65 mm
Test voltage (kV DC)	2.26
VSWR	<1.3 DC to 6 GHz
Contact Type	Coaxial 50 Ohm (Female Crimp) Type C
Cable type	RG 316 /U

Form & Material

Weight	2.03 g
--------	--------

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Conductor \varnothing max	0.58 mm
Dielectric \varnothing max	1.65 mm
Sheath \varnothing max	3.0 mm

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/pss-2b-250-ztme30.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.