



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Threaded
Jacket cable outside diameter [mm]	2.60 - 3.00 mm
Size	0V
Suggested matching part	FVN.0V.250.CLAC30

https://www.lemo.com/int_en/pvp-0v-250-cllc30.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax	Solder
Insert configuration value	0V.250 - 1 Coax (50 Ohm)
OHM	50

Form & Material

Shell style / Model id	PVP - Free socket with cable collet
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	Circular, female
Colour	Grey
Weight	14.78 g

Environment

Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C
Climatical Category	20/200/21
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr


Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	2.60 - 3.00 mm

https://www.lemo.com/int_en/pvp-0v-250-cllc30.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	B	e	L	S1	S2
mm.	10	M14x1.0	34	9	8
in.	0.39		1.34	0.35	0.31

Recommended By Lemo

Accessories

Compatible cap

[BRF.0V.200.NAV](#)

https://www.lemo.com/int_en/pvp-0v-250-cllc30.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.