



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Triax	1
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Threaded
Jacket cable outside diameter [mm]	3.10 - 3.50 mm
Size	0V
Suggested matching part	FVN.0V.650.CLAC35Z

Technical details

Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Insert configuration value	0V.650 - 1 Triax (50 Ohm)
OHM	50

Form & Material

Shell style / Model id	PVP - Free socket, cable collet and nut for fitting a bend relief
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	Circular, female
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	15.39 g

Environment

Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	20/200/21
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	3.10 - 3.50 mm

https://www.lemo.com/int_en/pvp-0v-650-cllc35z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	B	e	L	S1	S2
mm.	10	M14x1.0	34	9	7
in.	0.39		1.34	0.35	0.28

Recommended By Lemo

Accessories

Compatible cap	BRF.0V.200.NAV
----------------	--------------------------------