



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Locking system	Push-pull
----------------	-----------

Size	1
------	---

https://www.lemo.com/int_en/rgg-01-f99-yne.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Shell style / Model id	RGG.01 - Straight fixed coupler
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	4.23 g


Environment

Environmental sealing (IP rating)	IP50
-----------------------------------	------

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

Drawings



Dimensions

	A	e1	E_{max}	E_{min}	L	S2
mm.	7	M5x0.5	5.7	0.5	22	6
in.	0.28		0.22	0.02	0.87	0.24

https://www.lemo.com/int_en/rgg-01-f99-yne.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.