



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

Number of contacts Low Voltage	1
Wire Size/AWG	32 - 28
Size	SP
Series	REDEL SP - Inner Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-505-zzc.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-505-zzc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	0.5
Wire Size/AWG	32 - 28

## Form & Material

Shell style / Model id	SAN - Male crimp contact for REDEL SP series, standard barrel
Housing material	Gold plated [ISO 27874] brass
Keying	No keying
Weight	0.05 g

## Environment

Technical domain	Medical
Environmental sealing (IP rating)	No IP rating

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

# Recommended By Lemo

## Tools

Positionner	<a href="#">SOE.050.VC</a>
Crimp tool	<a href="#">DPC.91.701.V</a>

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-505-zzc.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-505-zzc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.