



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Wire Size/AWG	28 - 20
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.00 - 5.20 mm
Size	SP
Suggested matching part	<a href="#">SRN.M04.GLL.5G</a>
Series	REDEL SP - Inner Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	Solder
R (max)	2.8 mOhm
Insert configuration value	SP.M04 - 4 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	11.5 A
Test voltage contact-contact	2.26 (kV DC)
Max. Solid Conductor	0.50 mm <sup>2</sup> (AWG 20)
Max. Stranded Conductor	0.50 mm <sup>2</sup> (AWG 20)
Air clearance	0.95 mm
Creepage distance	0.95 mm
Bucket Dia.	1.1 mm (0.04in)
Contact Dia.	1.3 mm (0.0512in)
Wire Size/AWG	28 - 20
Gender	Standard

## Form & Material

Shell style / Model id	SA - Straight plug, key (N) or keys (P, S and T), with grey cable collet
Plug	Straight
Housing material	Proprietary sulfone, grey
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Grey collet nut
Weight	5.66 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.








## Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.00 - 5.20 mm

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.04.T22.047QGC	TPR	Grey	
CMN.04.T22.048QGZE	TPR (medical)	Grey	
140240	PVC	Black	
140250	PVC	Grey	
40140	PVC	Black	
40260	PVC	Black	
4080	PVC	Grey	
4221	PVC	Black	
4280	PVC	Black	
80080	PVC	Grey	
80082	PVC	Red	
80084	PVC	Black	

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.