



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|--------------------------------|
| Number of contacts Low Voltage | 4 |
| Wire Size/AWG | 28 - 20 |
| Gender | Standard |
| Plug | Plug - Straight |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 4.00 - 5.20 mm |
| Size | SP |
| Suggested matching part | SRN.M04.GLL.5G |
| Series | REDEL SP - Inner Push-Pull |

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage | 4 |
| Contact Termination Low voltage | Solder |
| R (max) | 2.8 mOhm |
| Insert configuration value | SP.M04 - 4 Low V. |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 11.5 A |
| Test voltage contact-contact | 2.26 (kV DC) |
| Max. Solid Conductor | 0.50 mm ² (AWG 20) |
| Max. Stranded Conductor | 0.50 mm ² (AWG 20) |
| Air clearance | 0.95 mm |
| Creepage distance | 0.95 mm |
| Bucket Dia. | 1.1 mm (0.04in) |
| Contact Dia. | 1.3 mm (0.0512in) |
| Wire Size/AWG | 28 - 20 |
| Gender | Standard |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | SA/Z - Straight plug, key (N) or keys (P, S and T), with cable collet and nut for fitting a bend relief |
| Plug | Straight |
| Housing material | Proprietary sulfone, grey |
| Locking system | Push-pull |
| Keying | 3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts) |
| Colour | Grey |
| Variant | Grey collet nut for bend relief |
| Weight | 5.29 g |

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.








Environment

| | |
|-----------------------------------|---------------------|
| Technical domain | Medical |
| Environmental sealing (IP rating) | IP50 |
| Endurance | >5000 mating cycles |
| Temperature range | -50°C / +170°C |
| Steam sterilization | > 100 times |

Cable fixation

| | |
|------------------------------------|-----------------------|
| Cable termination protection | For cable bend relief |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 4.00 - 5.20 mm |

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|---------------|--------|---|
| CMN.04.T22.047QGC | TPR | Grey | |
| CMN.04.T22.048QGZE | TPR (medical) | Grey |  |
| 140240 | PVC | Black |  |
| 140250 | PVC | Grey |  |
| 40140 | PVC | Black |  |
| 40260 | PVC | Black |  |
| 4080 | PVC | Grey | |
| 4221 | PVC | Black |  |
| 4280 | PVC | Black |  |
| 80080 | PVC | Grey | |
| 80082 | PVC | Red | |
| 80084 | PVC | Black | |

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-5gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.