



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Wire Size/AWG	26 - 22
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.50 mm
Size	SP
Matching parts	SRN.M04.GLL.6G
Series	REDEL SP - Inner Push-Pull

Technical details

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-6gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Electrical Configuration

Contact Termination Low voltage	Solder
Insert configuration value	SP.M04 - 4 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	11.5 Amps
Test voltage (kV rms) Contact-contact	1.60
Contact Type	Solder
Max. Conductor	1 mm ² (AWG 18)
Min. Conductor	0.36 mm ² (AWG 22)
Air clearance	0.96 mm
Creepage distance	0.96 mm
Bucket Dia.	1.1 mm (0.04in)
Contact Dia.	1.3 mm (0.0512in)
Number of contacts Low Voltage	4
Wire Size/AWG	26 - 22

Form & Material

Shell style / Model id	SA/Z - Straight plug, key (N) or keys (P, S and T), with cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Proprietary sulfone, gray
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Gray collet nut for bend relief
Weight	5.16 g

Environment

Technical domain	Medical
Environmental protection (IP rating)	IP50
Minimal temperature	-50°C / +170°C

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-6gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.50 mm








Recommended By Lemo

Accessories

Tools

Crimp tool	DPC.91.701.V
------------	------------------------------

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.04.T20.053PGZE		grey	
CMN.04.T20.053PNZE			
CMN.04.T20.053QGZE	TPR (medical)	Grey	
240500	PVC	Grey	
417920	PVC	Grey	
4220	PVC	Black	
CTR.75.030.121870G	PVC	Grey	

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-6gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.