



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Wire Size/AWG	26 - 22
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	6.60 - 7.50 mm
Size	SP
Matching parts	<a href="#">SKN.M04.GLLG</a>
Series	REDEL SP - Inner Push-Pull

## Technical details

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-7g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-7g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Solder
Insert configuration value	SP.M04 - 4 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	11.5 Amps
Test voltage (kV rms) Contact-contact	1.60
Contact Type	Solder
Max. Conductor	1 mm <sup>2</sup> (AWG 18)
Min. Conductor	0.36 mm <sup>2</sup> (AWG 22)
Air clearance	0.96 mm
Creepage distance	0.96 mm
Bucket Dia.	1.1 mm (0.04in)
Contact Dia.	1.3 mm (0.0512in)
Number of contacts Low Voltage	4
Wire Size/AWG	26 - 22

## Form & Material

Shell style / Model id	SA - Straight plug, key (N) or keys (P, S and T), with grey cable collet
Plug	Straight
Housing material	Proprietary sulfone, gray
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Gray collet nut
Weight	4.9 g

## Environment

Technical domain	Medical
Environmental protection (IP rating)	IP50
Minimal temperature	-50°C / +170°C

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-7g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-7g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	6.60 - 7.50 mm

# Recommended By Lemo

## Accessories

## Tools

Crimp tool	<a href="#">DPC.91.701.V</a>
------------	------------------------------

# Cables

Cable PartNumber	Material	Colour	Cable image
240750	PVC	Grey	

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-7g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m04-gla-7g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.