



Image for illustrative purpose only

## Summary

[Request a quote](#)

Number of contacts Low Voltage	8
Wire Size/AWG	30 - 22
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	6.60 - 7.50 mm
Size	SP
Suggested matching part	<a href="#">SRN.M08.GLL.7G</a>
Series	REDEL SP - Inner Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m08-gla-7g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m08-gla-7g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	Solder
R (max)	4.5 mOhm
Insert configuration value	SP.M08 - 8 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	5 A
Test voltage contact-contact	2.1 (kV DC)
Contact Type	Solder
Max. Solid Conductor	0.34 mm <sup>2</sup> (AWG 22)
Max. Stranded Conductor	0.34 mm <sup>2</sup> (AWG 22)
Air clearance	0.75 mm
Creepage distance	0.75 mm
Bucket Dia.	0.8 mm (0.032in)
Contact Dia.	0.9 mm (0.0354in)
Number of contacts Low Voltage	8
Wire Size/AWG	30 - 22

## Form & Material

Shell style / Model id	SA - Straight plug, key (N) or keys (P, S and T), with grey cable collet
Plug	Straight
Housing material	Proprietary sulfone, gray
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Gray collet nut
Weight	46.91 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m08-gla-7g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m08-gla-7g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	6.60 - 7.50 mm

# Cables

Cable PartNumber	Material	Colour	Cable image
108220	PVC	Black	

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m08-gla-7g.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m08-gla-7g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.