



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	10
Wire Size/AWG	26 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.50 mm
Size	SP
Suggested matching part	<a href="#">SLN.M10.BLMJ</a>
Series	REDEL SP - Inner Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m10-blc-6j.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m10-blc-6j.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Crimp
R (max)	6.5 mOhm
Insert configuration value	SP.M10 - 10 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4.2 A
Test voltage contact-contact	2.17 (kV DC)
Max. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Min. Conductor	0.14 mm <sup>2</sup> (AWG 26)
Air clearance	1.1 mm
Creepage distance	1.1 mm
Bucket Dia.	0.8 mm (0.032in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	26 - 22
Gender	Standard

## Form & Material

Shell style / Model id	SA - Straight plug, key (N) or keys (P, S and T), with yellow cable collet
Plug	Straight
Housing material	Proprietary sulfone, white
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	White - Yellow
Variant	Yellow collet nut
Weight	7.7 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m10-blc-6j.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m10-blc-6j.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.50 mm

# Recommended By Lemo






## Accessories

Replacement contact	<a href="#">SAN.520.ZZC</a>
---------------------	-----------------------------

## Tools

Positionner	<a href="#">SOE.070.VC</a>
Crimp tool	<a href="#">DPC.91.701.V</a>

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.10.T28.053QGZE	TPR (medical)	Grey	
110240	PTFE	White	
110280	PVC	Black	
210140	PVC	Grey	
210260	PVC	Black	

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/san-m10-blc-6j.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-m10-blc-6j.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.