



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	13
Wire Size/AWG	30 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	1.00 - 12.60 mm
Size	SP
Suggested matching part	SAN.M13.GLA.6B
Series	REDEL SP - Inner Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/sln-m13-gllb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	13
Contact Termination Low voltage	Solder
R (max)	6.5 mOhm
Insert configuration value	SP.M13 - 13 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4 A
Test voltage contact-contact	1.5 (kV DC)
Max. Solid Conductor	0.34 mm ² (AWG 22)
Max. Stranded Conductor	0.34 mm ² (AWG 22)
Air clearance	0.5 mm
Creepage distance	0.5 mm
Bucket Dia.	0.8 mm (0.032in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	SL_SP - Fixed socket, key (N) or keys (P, S and T), nut fixing, white front nut
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Proprietary sulfone, grey
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey - White
Variant	White front nut
Weight	4.63 g

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/sln-m13-gllb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	1.00 - 12.60 mm

Drawings



Dimensions

	a	B	N	e
mm.	2.2	18.5	23.5	M14x1
in.	0.09	0.73	0.93	

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.13.T22.072QGZE	TPR (medical)	Grey	

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/sln-m13-gllb.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.