



Image for illustrative purpose only

## Summary

[Request a quote](#)

Locking system	Push-pull
Size	SP

# Technical details

## Electrical Configuration

Rated current	4 A
Contact resistance	<8 mOhms

## Form & Material

Shell style / Model id	DCE - Positionner for female crimp contacts
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	13.22 g

## Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Radiation resistance	10e6 Gray
Working temperature	-20 deg C to + 125 deg C

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

[https://www.lemo.com/int\\_en/soe-050-vm.html](https://www.lemo.com/int_en/soe-050-vm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.