



Summary

[Request a quote](#)

[Catalog](#)

High Voltage	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Size	3Y
Matching parts	FFR.3Y.425.CFAE55G
Series	Y - High Voltage Unipole

Technical details

Electrical Configuration

Contact Termination High voltage	Solder
Insert configuration value	3Y.425 - 1 High Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	8 Amps
Test voltage (kV AC)	37
Contact Type	Solder
Creepage distance	25.5 mm
High Voltage	1

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/era-3y-425-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	ERA - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular
Weight	66.78 g

Environment

Technical domain	Specialties and Other
Environmental protection (IP rating)	IP50
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/era-3y-425-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.