



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts High Voltage	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	1.30 - 1.60 mm
Size	1Y
Suggested matching part	ERA.1Y.410.CLL
Series	Y - High Voltage Unipole

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-410-clac17.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts High Voltage	1
Contact Termination High voltage	Solder
Insert configuration value	1Y.410 - 1 High Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	8 A
Test voltage (kV DC)	15
Creepage distance	24.5 mm

Form & Material

Shell style / Model id	FFA - Straight plug with cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular
Colour	Grey
Weight	35.72 g

Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP50
Salt Spray Corrosion	>1000 hr



Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	1.30 - 1.60 mm

Drawings

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-410-clac17.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Dimensions

	A	L	M	S1
mm.	13	63.7	27.7	9
in.	0.51	2.51	1.09	0.35