



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts High Voltage	1
Plug	Plug - Straight
Locking system	Push-pull
Size	3Y
Matching parts	ERA.3Y.425.CLL
Series	Y - High Voltage Unipole

Technical details

Electrical Configuration

Contact Termination High voltage	Solder
Insert configuration value	3Y.425 - 1 High Voltage
Insulator	F: Silicon (LSR)/ Y series
Rated current	8 Amps
Test voltage (kV AC)	37
Contact Type	Solder
Creepage distance	25.5 mm
Number of contacts High Voltage	1

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffr-3y-425-cfae55r.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	FFR - Straight plug for cable crimping with bend relief and safety locking ring
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular
Weight	97.45 g



Environment

Technical domain	Specialties and Other
Environmental protection (IP rating)	IP50
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp

Drawings



Dimensions

	A	L	M	S1
mm.	19	120	92	15
in.	0.75	4.72	3.62	0.59

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffr-3y-425-cfae55r.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.