



## Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Size	1
Matching parts	<a href="#">FFS.01.250.DLAE31</a>

## Technical details

### Electrical Configuration

Coax	1
Insert configuration value	1.25 - 1 Coax (50 Ohm)

### Form & Material

Shell style / Model id	PCS - Free receptacle with cable crimping
Socket / Receptacle	Free
Housing material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	1.4 g

[https://www.lemo.com/int\\_en/pcs-01-250-dlle31.html](https://www.lemo.com/int_en/pcs-01-250-dlle31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +230°C

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp

Drawings



Dimensions

	A	L	S1	S2
mm.	5	18	4	4
in.	0.2	0.71	0.16	0.16