



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	8
Wire Size/AWG	30 - 22
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	SP
Matching parts	SAN.M08.GLA.5G
Series	REDEL SP - Inner Push-Pull

Technical details

Electrical Configuration

Insert configuration value	SP.M08 - 8 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	5 Amps
Contact Dia.	0.9
Number of contacts Low Voltage	8
Wire Size/AWG	30 - 22

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m08-glvg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Form & Material

Shell style / Model id	SK_SP - Fixed socket, key (N) or keys (P, S and T), with two nuts (back panel mounting), grey front nut and elbow print contacts
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Proprietary sulfone, gray
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Gray front nut
Weight	5.46 g

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

Drawings



Dimensions

	A	N	e	E _{max}	L
mm.	18.5	23.5	M14x1	8.5	36.5
in.	0.73	0.93		0.33	1.44

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m08-glvg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.