



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Size

00

https://www.lemo.com/int_en/bfg-00-100-pcsg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details


Form & Material

Shell style / Model id	BFG - Cap for plug
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	0.7 g

Environment

Environmental sealing (IP rating)	IP50
Temperature range	-50°C / +100°C

Drawings



Dimensions

	A	B	L	N
mm.	7.5	9.8	10	60
in.	0.3	0.39	0.39	2.36

https://www.lemo.com/int_en/bfg-00-100-pcsg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.