



Image for illustrative purpose only

# Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	9
Wire Size/AWG	34 - 28
Gender	Standard
Locking system	Push-pull
Size	0K
Series	K - Outdoor keyed

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	9
Insert configuration value	0K.309 - 9 Low Voltage
Rated current	2.5 A
Contact Dia.	0.5
Wire Size/AWG	34 - 28
Gender	Standard

## Form & Material

Shell style / Model id	0K - DONGLE THOMSON® HD for MEERKAT
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr


## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-0k-309-ca00th.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-0k-309-ca00th.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Recommended By Lemo

### Accessories

---

Compatible cap

[BFG.0K.100.NAS](#)

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-0k-309-ca00th.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-0k-309-ca00th.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.