



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Wire Size/AWG	4 - 4
Locking system	Ratchet
Size	4M
Suggested matching part	EGG.4M.P06.ZZM
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-4m-p06-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Max. Conductor High Power	25 mm ² (AWG 4)
Min. Conductor High Power	25 mm ² (AWG 4)
Contact Dia.	6
Wire Size/AWG	4 - 4

Form & Material

Shell style / Model id	FG - Male High Power crimp contact for 4M series
Housing material	Gold plated [ISO 27874] bronze
Locking system	Ratchet

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Thermal shock	5 cycles: -65Â°C to +150Â°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Note	Recommended crimping tool: Klauke K05 - K06 - K35/4

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-4m-p06-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Tools

Extraction tool

[DCC.91.64H.PLC](#)

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-4m-p06-zzc.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.