



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Fiber optic	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	00

[https://www.lemo.com/int\\_en/pfg-00-bb4-ccse30z.html](https://www.lemo.com/int_en/pfg-00-bb4-ccse30z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Fiber optic	1
Insert configuration value	FO/BB4 - 1 FO 126 um hole
Insulator	C: Zirconia Ceramic
Core/Cladding (um)	50/125
Ferrule Material	Zirconia Ceramic
Hole dia.(um)	126

## Form & Material

Shell style / Model id	PF - Fixed receptacle, with two nuts, with bend relief included (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	10.63 g

## Environment

Environmental sealing (IP rating)	IP50
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Crimp

# Drawings

[https://www.lemo.com/int\\_en/pfg-00-bb4-ccse30z.html](https://www.lemo.com/int_en/pfg-00-bb4-ccse30z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Dimensions

	A	L	e
mm.	10	53.5	M7x0.5
in.	0.39	2.11	

## Recommended By Lemo

### Accessories

Compatible cap	<a href="#">BRA.00.200.PCSG</a>
----------------	---------------------------------

### Tools

Spanner 2	<a href="#">DCM.65.088.AZ4</a>
Spanner wrench	<a href="#">Socket for torque wrench DCM.00.M07.4</a>

[https://www.lemo.com/int\\_en/pfg-00-bb4-ccse30z.html](https://www.lemo.com/int_en/pfg-00-bb4-ccse30z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.