



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Fluidic	1
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.50 mm
Size	1P
Suggested matching part	<a href="#">PLG.A0.1GZ.ZV</a>
Series	REDEL P - Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-a0-1gz-zc65v.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-a0-1gz-zc65v.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Fluidic	1
Insert configuration value	1P.A01 - 1 Fluidic contact
Gender	Standard

## Form & Material

Shell style / Model id	PA - Straight plug with cable collet (fluidic)
Plug	Straight
Housing material	PSU (Polysulfone), gray
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey - Green
Variant	Green collet nut
Weight	6.88 g

## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +150°C
Pressure	2 bars
R leak (He) (max)	0.0000001 mbar*l/s (if vacuum-tested)
Steam sterilization	Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.50 mm

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-a0-1gz-zc65v.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-a0-1gz-zc65v.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Tools

---

Spanner

[DCP.91.001.TN](#)

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-a0-1gz-zc65v.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-a0-1gz-zc65v.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.