

Image for illustrative purpose only

Summary

[Request a quote](#)

Number of contacts Low Voltage	22
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	SP
Suggested matching part	SAN.M22.GLA.5V
Series	REDEL SP - Inner Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m22-glvn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Contact Termination Low voltage	PCB - Straight
R (max)	8.5 mOhm
Insert configuration value	SP.M22 - 22 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Contact Type	Print (straight)
Contact Dia.	0.5 mm (0.0196in)
Number of contacts Low Voltage	22

Form & Material

Shell style / Model id	SK_SP - Fixed socket, key (N) or keys (P, S and T), with two nuts (back panel mounting), green front nut and straight print contacts
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Proprietary sulfone, gray
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Green front nut
Weight	4.84 g

Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times



Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m22-glnv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	a	B	N	e	E_{max}
mm.	4.1	18.5	23.5	M14x1	8.5
in.	0.16	0.73	0.93		0.33

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m22-glnv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.