



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	10
Nb of contacts Fluidic	1
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.30 - 9.20 mm
Size	2P
Series	REDEL P - Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/cab-015-nlc-c92r.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cab-015-nlc-c92r.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Crimp
Nb of contacts Fluidic	1
Insert configuration value	2P.015 - 1 Fluidic, 10 Low V.
Insulator	L: PEEK for solder contacts
Rated current	5 A
Test voltage contact-contact	1.63 (kV DC)
Air clearance	0.9 mm
Creepage distance	0.9 mm
Gender	Standard

## Form & Material

Shell style / Model id	CA - Straight plug with cable collet
Plug	Straight
Housing material	PSU (Polysulfone), black
Locking system	Push-pull
Keying	B: 3 keys (alpha=0, gamma=60, Plug: male contacts, Receptacle: female contacts)
Colour	Black - Red
Weight	10.88 g

## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
Temperature range	-50°C / +150°C

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.30 - 9.20 mm

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/cab-015-nlc-c92r.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cab-015-nlc-c92r.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Recommended By Lemo

### Accessories

Replacement contact	<a href="#">FGG.2B.555.ZZC</a>
---------------------	--------------------------------

### Tools

Positionner	<a href="#">DCE.91.072.BVC</a>
-------------	--------------------------------

Extraction tool	<a href="#">DCC.07.04B.LAG</a>
-----------------	--------------------------------

Crimp tool	<a href="#">DPC.91.701.V</a>
------------	------------------------------

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/cab-015-nlc-c92r.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cab-015-nlc-c92r.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.