



Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	1

Technical details

Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	1.25 - 1 Coax (50 Ohm)
Contact Type	Solder

Form & Material

Shell style / Model id	ECP.01 - Fixed receptacle, nut fixing (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	1.04 g


https://www.lemo.com/int_en/ecp-01-250-nll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +230°C
Salt Spray Corrosion	>144 hr

Drawings



Dimensions

	A	e	L	M	Emax
mm.	7	M5x0.5	10.5	5.7	3.5
in.	0.28		0.41	0.22	0.14

https://www.lemo.com/int_en/ecp-01-250-nll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.