



Summary

[Request a quote](#)

[Catalog](#)

| | |
|---------------------|-----------------------------------|
| Coax | 1 |
| Socket / Receptacle | Socket / Receptacle - Free |
| Locking system | Push-pull |
| Size | 1 |
| Matching parts | FFS.01.250.DLAE31 |

Technical details

Electrical Configuration

| | |
|----------------------------|------------------------|
| Coax | 1 |
| Insert configuration value | 1.25 - 1 Coax (50 Ohm) |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | EPA.01 - Straight receptacle for printed circuit |
| Socket / Receptacle | Free |
| Housing material | Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | Circular, female |
| Weight | 1.5 g |

https://www.lemo.com/int_en/epa-01-250-dln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Environmental protection (IP rating)

IP50

Minimal temperature

-55°C / +230°C

https://www.lemo.com/int_en/epa-01-250-dln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.