



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|--------------------------------|------------------------------------|
| Number of contacts Low Voltage | 8 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Elbow |
| Locking system | Push-pull |
| Size | 1B |
| Suggested matching part | FGG.1B.308.CLAD62Z |
| Series | B - Indoor keyed |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/epg-1b-308-hln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---|----------------------------|
| Number of contacts Low Voltage | 8 |
| Contact Termination Low voltage | PCB - Straight |
| R (max) | 6.1 mOhm |
| Insert configuration value | 1B.308/EPG - 8 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 2 A |
| Test voltage contact-body shell | 1.3 kV rms |
| Test voltage contact-contact | 1.3 kV rms |
| Contact Dia. | 0.7 mm (0.028in) |
| Number of differentiated pairs (High speed) | 4 |
| Gender | Standard |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | EP - Elbow receptacle for printed circuit (solder or screw fixing) |
| Socket / Receptacle | Elbow |
| Housing material | PPS (Polyphenylene) shell, other pieces nickel plated [SAE AMS QQ N 290] brass |
| Locking system | Push-pull |
| Keying | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Weight | 12.33 g |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/epg-1b-308-hln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

| | |
|-----------------------------------|--|
| Technical domain | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | 5000 mating cycles |
| Temperature range | -55°C / +250°C (max. temperature valid for short periods of use.) |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 75 dB (10 MHz) |
| Shielding (min) | 40 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |
| Salt Spray Corrosion | >144 hr |

Recommended By Lemo

Accessories

Compatible cap [BRE.1S.200.NAS](#)

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/epg-1b-308-hln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.