



Summary

[Request a quote](#)[Catalog](#)

Triax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.10 - 7.50 mm
Size	1E
Matching parts	ERA.1E.650.CTL
Series	E - Outdoor Stepped Insert

Technical details

Electrical Configuration

Triax	1
Contact Termination Triax	Solder
Insert configuration value	1E.650 - 1 Triax (50 Ohm)
Insulator	T: PTFE
Rated current	6 Amps
Impedance	50 Ohm
VSWR	$1.01 + 0.17 * f/\text{GHz}$
Vtest	1200 V (AC), 1690 V (DC)
Contact Type	Solder
Cable type	Cable type: A RGT 178, RGT 174,Belden 9222 S

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-1e-650-ctak75z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	FFA - Straight plug with oversize cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, male
Variant	Nut for fitting a bend relief
Weight	34.26 g


Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental protection (IP rating)	IP68
Minimal temperature	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.10 - 7.50 mm

Drawings



https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-1e-650-ctak75z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.