



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	8
Wire Size/AWG	24 - 20
Gender	Reverse Gender
Plug	Plug - Straight
Locking system	Ratchet
Jacket cable outside diameter [mm]	6.50 - 13.00 mm
Size	2M
Suggested matching part	<a href="#">EGS.2M.308.XLC</a>
Series	M - Rugged Ratchet coupling

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/fgs-2m-308-xlmt.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgs-2m-308-xlmt.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	8
Contact Termination Low voltage	Crimp
R (max)	4.8 mOhm
Insert configuration value	2M.308 - 8 Low Voltage
Insulator	L: PEEK
Rated current	10 A
Test voltage (kV rms) Contact-contact	1.95
Test voltage (kV rms) Contact-shell	1.1
Contact retention	30 N
Max. Conductor	0.5 mm <sup>2</sup> (AWG 20)
Min. Conductor	0.25 mm <sup>2</sup> (AWG 24)
Bucket Dia.	1.1 mm (0.043in)
Contact Dia.	0.9 mm (0.035in)
Wire Size/AWG	24 - 20
Gender	Reverse Gender

## Form & Material

Shell style / Model id	FG - Straight plug with arctic grip and mold stop
Plug	Straight
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	S: 3 keys (beta=155, gamma=50, plug: female contacts, receptacle: male contacts)
Colour	Grey
Weight	10.3 g

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/fgs-2m-308-xlmt.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgs-2m-308-xlmt.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.




## Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-55°C / +200°C
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [ 3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

## Cable fixation

Cable termination protection	For overmolding
Fixation type	Mold stop (overmolding)
Jacket cable outside diameter [mm]	6.50 - 13.00 mm

## Drawings



## Dimensions

	A	B	C	D	F	Ls	Lr	M	P	X
mm.	18.9	14	17.2	13	15.5	27.5	27.5	10.1	3.9	7.1
in.	0.74	0.55	0.68	0.51	0.61	1.08	1.08	0.4	0.15	0.28

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/fgs-2m-308-xlmt.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgs-2m-308-xlmt.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

Accessories	
Replacement contact	<a href="#">EGN.0M.660.ZZM</a>
Compatible cap	<a href="#">BGF.2M.100.XAV</a>
Tools	
Positionner	<a href="#">DCE.91.090.3MVM</a>
Extraction tool	<a href="#">DCC.09.05B.LAG</a>
Crimp tool	<a href="#">DPC.91.701.V</a>