



## Summary

[Request a quote](#)

[Catalog](#)

Triax	1
Plug	Plug - Elbow
Locking system	Push-pull
Matching parts	<a href="#">ERN.00.650.CLL</a>
Series	00 - NIM-CAMAC

## Technical details

### Electrical Configuration

Triax	1
Contact Termination Triax	Solder
Insert configuration value	0.65 - 1 Triax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	3 Amps
Impedance	50 Ohm
VSWR	1.1 + 0.11 * f/GHz
Vtest	1200 V (AC), 1700 V (DC)
Contact Type	Triaxial 50 Ohm (Solder)
Cable type	Cable type: A RGT 403 S
Contact Dia.	0.5 mm (0.02" in)

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/fla-00-650-clac35.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/fla-00-650-clac35.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Form & Material

Shell style / Model id	FLA - Elbow plug with cable collet
Plug	Elbow
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	5.76 g

## Environment

Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +250°C
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/fla-00-650-clac35.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/fla-00-650-clac35.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.