



Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Plug	Plug - Elbow
Locking system	Push-pull
Size	1
Matching parts	ERA.01.250.DLL

Technical details

Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	1.25 - 1 Coax (50 Ohm)
Contact Type	Solder

Form & Material

Shell style / Model id	FLS.01 - Elbow plug, for cable crimping
Plug	Elbow
Housing material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	2.28 g

https://www.lemo.com/int_en/fls-01-250-dlae31.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Environmental protection (IP rating)

IP50

Minimal temperature

-55°C / +230°C

Cable fixation

Cable termination protection

Standard back nut (no additional protection)

Fixation type

Crimp

Drawings



Dimensions

	A	L	H	M
mm.	7.5	12.1	12	6.6
in.	0.3	0.48	0.47	0.26

https://www.lemo.com/int_en/fls-01-250-dlae31.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.