



## Summary

[Request a quote](#)[Catalog](#)

Coax	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.60 - 22.60 mm
Size	3E
Series	E - Outdoor Stepped Insert

## Technical details

### Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	3E.250 - 1 Coax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	26 Amps
Impedance	50 Ohm
VSWR	1.06 + 0.5 * f/GHz
Vtest	3000 V (AC), 4200 V (DC)
Contact Type	Solder
Cable type	Cable type: A RG 213/U, RG 115 A/U, RG 11 A/U, RG 144/U, RG 165 /U S

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/hgp-3e-250-cllpe.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/hgp-3e-250-cllpe.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Form & Material

Shell style / Model id	HGP - Fixed receptacle, nut fixing, watertight or vacuum-tight
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Variant	Watertight unmated (connector to device)
Weight	74.39 g



## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental protection (IP rating)	IP68
Minimal temperature	-20°C / +80°C
Climatical Category	20/80/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

## Cable fixation

Jacket cable outside diameter [mm]	2.60 - 22.60 mm
------------------------------------	-----------------

## Drawings



[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/hgp-3e-250-cllpe.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/hgp-3e-250-cllpe.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Dimensions

	<b>B</b>	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S3</b>	<b>A</b>
mm.	34	M24x1.0	15.5	39.5	6	22.5	30	31
in.	1.34		0.61	1.56	0.24	0.89	1.18	1.22