



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|--------|---------------------------|
| Size | 3S |
| Series | S - Indoor Stepped Insert |

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/brf-3s-200-nas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details


Form & Material

| | |
|------------------------|--|
| Shell style / Model id | BRF - Cap for free receptacle |
| Housing material | Brass (nickel plated [SAE AMS QQ N 290]) collet and crimping tube, brass (chrome plated [SAE AMS 2460]) collet nut |
| Keying | No keying |
| Colour | Grey |
| Weight | 21.52 g |

Environment

| | |
|-----------------------------------|---|
| Technical domain | Audio Video, Energy and Industrial, Semiconductor, Test and Measurement |
| Environmental sealing (IP rating) | IP61 |
| Temperature range | -55°C / +135°C |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 75 dB (10 MHz) |
| Shielding (min) | 40 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |
| Salt Spray Corrosion | >144 hr |

Drawings



No keying

Dimensions

| | A | B | L | M | N |
|-----|------|------|------|------|------|
| mm. | 22 | 14 | 18 | 8 | 120 |
| in. | 0.87 | 0.55 | 0.71 | 0.31 | 4.72 |

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/brf-3s-200-nas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.