



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	5
Gender	Reverse Gender
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Ratchet
Size	1M
Suggested matching part	<a href="#">FMS.1M.305.XLM</a>
Series	M - Rugged Ratchet coupling

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/eds-1m-305-xld.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/eds-1m-305-xld.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	PCB - Straight
Insert configuration value	1M.305 - 5 Low Voltage
Insulator	L: PEEK
Rated current	9 A
Test voltage (kV rms) Contact-contact	1.3
Test voltage (kV rms) Contact-shell	1.3
Contact Type	Print (straight)
Contact Dia.	0.9
Number of contacts Low Voltage	5
Gender	Reverse Gender

## Form & Material

Shell style / Model id	ED - Fixed receptacle with square flange for printed circuit
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	3 keys (beta=155, gamma=50, plug: female contacts, receptacle: male contacts)
Weight	4.35 g



[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/eds-1m-305-xld.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/eds-1m-305-xld.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +200°C
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [ 3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

## Drawings



## Dimensions

	A	B	C	G	H	K	Ls	Lr	N	P	SV
mm.	23.8	5.95	14.2	12.8	12.9	1.5	18.3	18.3	18.4	5.3	3.3
in.	0.94	0.23	0.56	0.5	0.51	0.06	0.72	0.72	0.72	0.21	0.13

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/eds-1m-305-xld.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/eds-1m-305-xld.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.